



Main

Range of product	Preventa XY2
Product or component type	Simple rope pull switch
Device short name	XY2CD
Overvoltage category	Class I conforming to EN/IEC 61140 Class I conforming to NF C 20-030

Complementary

Trigger cable maximum length	6 m
Resistance to wrenching	237 daN operating head 36 daN operating ring
Cable entry number	3
[Ie] rated operational current	3 A at 240 V, AC-15, A300 conforming to EN/IEC 60947-5-1 appendix A 0.27 A at 250 V, DC-13, Q300 conforming to EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	400 V (pollution degree 3) conforming to EN/IEC 60947-1 300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14
Compatibility code	XY2CD

Environment

IP degree of protection	IP66 conforming to IEC 60529
-------------------------	------------------------------

Packing Units

Package 1 Weight	298 g
Package 2 Weight	2.825 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile