


Type Number..... 4276
Designation IEC..... LR44
System..... Manganese Dioxide/
 Zinc/KOH-Electrolyte



Nominal Voltage..... 1,5V
Typical Capacity C..... 130 mAh

Temperature Ranges min max.
 Storage..... -10°C 65°C
 Discharge..... -10°C 65°C

Dimensions min max.
 Diameter..... 11,25 11,60
 Height (A/B)..... 5,00 5,40

Weight (approx.)..... 2,02 g

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage: 1.2 V	
Continuous 24h/d, 7d/w	6800 Ω	Time: [h]	650 h

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

All Data contained herein is for single cells
 For battery applications, performance data may vary from single cell data, depending on specific battery configuration