



Product data sheet

Power tools for trade & industry

Orbital Sander

PRO GSS18V-18



Optimal control on larger surfaces

The most important data

Orbit diameter	2 mm
No-load speed	5000 – 10000 rpm

Part Number 0 601 9R7 000

Technical data

Technical data

Battery voltage	18.0 V
No-load orbital stroke rate	10,000 – 20,000 opm
Orbit diameter	2 mm
Packaging dimensions (width x length x height)	173 x 256 x 149 mm
Weight excl. battery	1.2 kg
No-load speed	5000 – 10000 rpm
BITURBO	No

Sanding surface

Sanding surface	167 cm ²
-----------------	---------------------

Noise/vibration information

Sanding panel materials

Vibration emission value ah	3.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Optimal control thanks to its low height of up to 118 mm and excellent tool balance
- Less fatigue with low vibration value up to 3.5 m/s²
- Efficient dust management solution with high dust pick-up rate of 85 % and easy dust disposal

HEAVY DUTY

92 x 182 mm

Ø 2.0 mm

ERGONOMIC

VIBRATION CONTROL

AMP Share
POWER TO BOSCH

SPEED SELECTION

CONSTANT SPEED

BRUSHLESS MOTOR



PROFESSIONAL 18V SYSTEM

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

