




LOC	DIST	REVISIONS							
		P	LTR	DESCRIPTION			DATE	DWN	APVD
FT	4						4/2/91	—	
			H1	REVISED PER ECO-11-004820			11MAR11	RK	HMR



- △1 HOUSING & RETENTION INSERT: THERMOPLASTIC, BLACK.
THREADED INSERTS: BRASS.
2. CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT
AND REAR FACES OF CONNECTOR.
3. WILL ACCEPT (28) SIZE 20 PIN CONTACTS.
- △4 AMP AND PART NUMBER ANY EDGE.



YES	YES	205840-5
NO	YES	205840-4
NO	NO	205840-3
PERIPHERAL SEAL	4-40 THREADED INSERTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.STAUB BG 4/3/91	 TE Connectivity								
		CHK W.G.LENKER 7-24-92									
DIMENSIONS: INCHES		APVD K.BEAVER 7-24-92	NAME								
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RECEPTACLE ASSEMBLY, STD SEX, SERIES 2, 17-28, CPC							
		0 PLC ± -									
		1 PLC ± -									
		2 PLC ± -		SIZECAGE CODEDRAWING NORESTRICTED TO							
		3 PLC ± .005									
		4 PLC ± -									
MATERIAL		FINISH		APPLICATION SPEC		A200779C-205840					
				—							
		—		WEIGHT —							
		CUSTOMER DRAWING				SCALE 2:1		SHEET 1 of 1		REV H1	