

## Features

- **Waterproof IP67 rating guarantees protection against extended immersion under higher pressures**
- **Cable out diameter 1.4 mm**
- **Voltage rating of 60V**
- **Current rating of 3A**
- **Gold-plated bronze contacts for corrosion resistance**
- **Threaded mating type**
- **Operating temperature range from -25°C to 80°C**
- **Gold contact plating**
- **PVC cable jacket**
- **200mm length**
- **Conforms to standards IEC 61076-2-104**

## RS PRO Female M8 4 Pin Cable

RS Stock No.: 2825372



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

The 4 pin female M8 cable had been widely used for automotive and sensor application, it's unshielded.

## General Specifications

Number of Contacts	4
Shielding	Unshielded
Housing Material	PA66+GF, Black
Contact Material	Bronze
Contact Plating	Gold
Pole Format	4P
Contact Gender	Female
Mating Type	Threaded
Body Orientation	Straight
Mating Cycles	500
Cable Jacket	PVC
Color	Brown, White, Blue, Black
Application	Marine, Automotive

## Electrical Specifications

Plug/Socket	Socket
Current Rating	3A
Voltage Rating	60V
Insulation Resistance	$\geq 100M\Omega$

