


#### **FEATURES**

- Sheet filter
- Polyester media
- Hollow spiralcrimped PET media
- Initial pressure drop of 69 Pa
- Final pressure drop of 250 Pa
- Filter grade of G4
- Nominal height of 98in
- Nominal width of 79in
- Nominal depth of 2in
- Actual height of 2500mm
- Actual width of 2000mm
- Actual depth of 50mm

# RS PRO Sheet Filter, PET Media, G4 Grade, 2500 x 2000 x 50mm

RS Stock No.: 730-2915



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

This hollow spiral-crimped sheet filter is a durable solution for your heating, ventilation and air conditioning (HVAC) systems. As part of the RS PRO range, this HVAC air filter has been rigorously tested. Its wadding is made from polyester filters that are thermally bonded to create a long-lasting material while also enabling the filter to hold large amounts of air and remain lightweight.

Measuring 2500 mm x 2000 mm x 50 mm, this sheet filter is suitable for use in large-scale HVAC systems and can be safely and easily cut to size as required. As a G4-grade filter, this product will stop particles that are visible with the naked eye and is used to remove dust and debris from the air.

#### **General Specifications**

Filter Type	Sheet
Filter Grade	G4
Media Material	PET
Colour	White
Applications	General prefilter for HVAC and kitchen hoods

#### **Mechanical Specifications**

Nominal Dimensions	98in x 79in (Height x Width)
Nominal Height	98in
Nominal Width	79in
Nominal Depth	2in
Initial Pressure Drop	69Pa
Final Pressure Drop	250Pa

Actual Dimensions	
Dimensions	2500mm x 2000mm x 50mm
Actual Height	2500mm
Actual Width	2000mm
Actual Depth	50mm

## **HVAC Air Filters**



### Approvals

	5 110 0
Standards Met	RoHS Compliant
	' ·