

Removable Notched Cable Ties (CCD type)



General features

CCD9 series

- ✓ Material: black polyamide 11/12.
- ✓ Halogen free.
- ✓ Melting temperature: 180°C.
- ✓ Flammability rating: UL 94 HB.
- ✓ Limit oxygen index (LOI): 22.5%.
- ✓ Operating temperature : -45°C to +80°C.
- ✓ Assembling temperature : -30°C to +60°C.
- ✓ Regain of humidity: ≈ 1%.
- ✓ Resistance to external agents: bases, acids, oils, hydrocarbons, salt fog.
- ✓ Resistance to ultra-violet and ozone.
- ✓ Non resistant to chlorinated solvents.

**CCD9
Series**

Compliant
**EDF HN
33 S 62
(07-76)**



Item code	100 /box	Part No.	Max bundle Ø (mm)	Length (mm)	Width (mm)
7100031		CCD9-42	10 - 42	187	9
7100041		CCD9-62	20 - 62	251	9
7100051		CCD9-92	20 - 92	344	9

General features

CCD9-A series

- ✓ Material: white polyamide (internal use).
- ✓ Halogen free.
- ✓ Melting temperature: 250°C.
- ✓ Flammability rating: UL 94 V0.
- ✓ Limit oxygen index (LOI): 31%.
- ✓ Operating temperature: -40°C to +110°C.
- ✓ Assembling temperature : -10°C to +50°C.
- ✓ Resistance to external agents: bases, acids, oils, hydrocarbons, salt fog.

**CCD9-A
Series**

Homologated
**EDF
(SEPTEN)**



Item code	100 /box	Part No.	Max bundle Ø (mm)	Length (mm)	Width (mm)
7110121		CCD9-42A	10 - 42	187	9
7110131		CCD9-62A	20 - 62	251	9
7110141		CCD9-92A	20 - 92	344	9



Packing

Unless otherwise stated,
all dimensions are in millimeters.