

11131
Abrasive shaft-mounted wheels, abrasive pink corundum grains, ceramic bonded, globe-shaped
EN 12413

For universal use

shaft Ø 6 x 40 mm

	art.	Ø mm	h mm	max. rpm Lo=13 mm	
111310010	11131 10X10	10	10	95.400	AR60P5V
111310015	11131 15X15	15	15	63.600	AR60P5V
111310020	11131 20X20	20	20	47.700	AR46P5V
111310025	11131 25X25	25	25	37.200	AR36/46P5V
111310030	11131 30X30	30	30	26.200	AR36/46P5V

