
2101 : Steel Pipe Cutter





Description

Max thickness: 5 mm.
For quickly cutting steel pipes (gas- API-etc...) cleanly and squarely. Also cuts stainless steel pipes (> 2 mm thick) with cutting wheels 210123 and grey cast iron with cutting wheels 210122.

References

Sku	A pipe "	A pipe mm	L mm	H mm	E maxi mm	kg
210110	1/8 - 1.1/4	10 - 42	310	118	5	1,740
210120	1/2 - 2	21 - 60	400	150	5	3,020
210130	3/4 - 3	27 - 90	460	177	5	4,220

