

2514: Multi-diameter Bending Plier







The + product :

Multi-purpose: 1 tool for 3 dimensions: Ø 6, 8, 10 mm.

Comfort: Light and compact in the toolbox instead of 3 single diameter bending pliers.

Description

For hardened and annealed copper pipes: Ø 6, 8, 10 mm / wall thickness: 1 mm.

Lightweight alloy body.

180° bending angle.

0 to 180° graduations.

Ideal for many applications: air conditioning, refrigeration, gas supply, and compressed air circuit.

References

Sku	Size mm	kg
251406	275 x 68 x 61	0,450

