



Datasheet

RS PRO Long Nose Precision Pliers





RS PRO long nose slim precision pliers are ergonomically designed bi- material pliers which offer high performance for all-day use. Featuring an asymmetric handle profile for increased comfort and less fatigue over long periods of use, the grips also have finger guards integrated into the design to prevent slipping. Ideal for a variety of precision applications where component handling and wire manipulation are common. The gripping jaws are longer and slimmer for improved access in constricted spaces and for working with smaller components.

- Assymetric grip profile fits the contours of the hand for improved ergonomics
- Bi-material handle for comfortable working all daylong
- High leverage pliers offering high performance
- Hot drop forged, hardened and tempered steel
- Induction hardened, precision milled gripping face
- Screw joint design
- Integral springs to return handles to open position
- Long/slim tip profile for working in confined spaces and gripping very small components

RS CODE NO	L mm	∆gr∆
2006023	155	81





Attributes	
Cutting Capacity:	N/A
ESD Safe	N
Height Safe:	N
Jaw Depth:	12 mm
Jaw Length:	28 mm
Material::	Sheet Steel
Non Sparking:	N
Overall Length:	155 mm
Overall Width:	57
VDE/1000V Approved:	N