

Description	The LabelPOINT 300 is the perfect labelmaker for trade and retail professionals. Compact in size and packed with useful features, the LabelPOINT 300 prints labels up to 3/4"(19mm) with bar codes, electrical symbols, background effects and up to 4 lines of print. Plus it includes a 10-label memory and a built-in tax calculator.
Key Features	<ul style="list-style-type: none"> • Compact, handheld design. • ABC keyboard with large keys for easy data entry. • Horizontal, vertical and mirror printing. • Left, center and right justification. • 2-line, 15-character LCD display for editing and label preview. • Built-in memory stores last label plus 10 additional labels. • 5 print styles, 6 background effects plus many electrical symbols. • Auto-numbering, repeat printing and tax calculator. • UPCA/E, EAN8/13, Code-39, and Code-128 bar codes. • Prints on 1/4"(6mm), 3/8"(9mm), 1/2"(12mm) and 3/4"(19mm) D1 tapes. • Uses 6AA batteries or optional power adapter. • Dimensions (WHD): 4.5"(114mm) x 8.3"(212mm) x 2.8"(70mm)
Options and Accessories	DYMO 1/4"(6mm), 3/8"(9mm), 1/2"(12mm) and 3/4"(19mm) D1 tapes.

Product Specifications

Printer Attributes

Printer Speed

Emulations DYMO

Add-on Consumables DYMO 1/4"(6mm), 3/8"(9mm), 1/2"(12mm) and 3/4"(19mm) D1 tapes.

133326