



## **GEE99FR-CY Slotted Grommet, Natural, FR PE, 0.09" Max Panel, PK1**

**GEE99FR-CY**

Slotted grommet edging, .099" thickness, flame retardant polyethylene, natural.

### **Specifications**

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Product Type                             | Slotted Grommet Edging                                                                                                       |
| Color                                    | Natural                                                                                                                      |
| Flammability Rating                      | UL94V-0                                                                                                                      |
| Material                                 | Polyethylene                                                                                                                 |
| Maximum Compatible Panel Thickness (In.) | 0.099                                                                                                                        |
| Maximum Compatible Panel Thickness (mm)  | 2.5                                                                                                                          |
| Minimum Compatible Panel Thickness (In.) | 0.062                                                                                                                        |
| Minimum Compatible Panel Thickness (mm)  | 1.6                                                                                                                          |
| Maximum Operating Temperature (°C)       | 50                                                                                                                           |
| Maximum Operating Temperature (°F)       | 122                                                                                                                          |
| Minimum Operating Temperature (°C)       | -20                                                                                                                          |
| Minimum Operating Temperature (°F)       | -4                                                                                                                           |
| Overall Length (ft.)                     | 100                                                                                                                          |
| Overall Length (m)                       | 30.48                                                                                                                        |
| Overall Width (In.)                      | 0.17                                                                                                                         |
| Overall Width (mm)                       | 4.3                                                                                                                          |
| Overall Height (In.)                     | 0.19                                                                                                                         |
| Overall Height (mm)                      | 4.7                                                                                                                          |
| Resistance Properties                    | Flame-Retardant                                                                                                              |
| Standards Met                            | RoHS Compliant                                                                                                               |
| Application                              | To Protect and Prevent Wires and Cables from Chafing Against Sharp Edges of Panel Walls and Knockouts.                       |
| Part Features                            | Provides protection for cables being installed where there might be sharp edges with irregular shaped and round panel holes. |

**Packaging Detail**

|                       |             |
|-----------------------|-------------|
| UPC                   | 07498310756 |
| Std. Pkg. Qty.        | 1           |
| Std. Pkg. Volume (cf) | 0.3169      |
| Std. Ctn. Qty.        | 0           |
| Std. Ctn. Volume (cf) | 0.0000      |