

DATA SHEET: FLS##BK SERIES

IP65 LED Floodlight



MLA part code:	FLS15BK	FLS30BK	FLS50BK	FLS70BK	FLS130BK
Description:	15W LED	30W LED	50W LED	70W LED	130W LED
Finishes:	Black				
Weight (kg):	0.6	1.28	2.17	3.03	4.87
Wattage (W):	15	30	50	70	130
Overall dimensions (mm):	115(l) 99(h) 88(p)	181(l) 154(h) 112(p)	223(l) 196(h) 135(p)	285(l) 235(h) 140(p)	285(l) 390(h) 110(p)
ERP class:	A	A+	A+	A+	A+
Lumen output (lm):	1200	2600	4700	6700	11600
CCT:	6000K				
LED colours:	Day Light				
Input voltage:	Mains 230V 50Hz				
Construction:	Die cast Aluminium				
Driver required:	No				
Class:	Class I				
IP rating:	IP65				
Life span:	25,000 hrs				
Pre wired:	Yes with 500mm cable				
Warranty:	3 Year				
Dimmable:	No				
Instruction sheet:	Yes				
Origin of manufacture:	China				
Quality assurance system:	ISO9001				
Declaration of conformity (held on file):	Yes				
Manufactured in accordance with:	EN60598-2-5				

