



Product data sheet

Power tools for trade & industry

ISN-24 G Industrial Smart Controller

INDUSTRIAL ISN-24 G Industrial Smart Controller



Data-driven tightening process control made easy and affordable

The most important data

NFC frequency	13.56 MHz
Wi-Fi frequency	2.4 GHz
Connection Interface	I/O port, ...

Part Number 1 600 A03 9KL

Technical data

Technical data

Length x Width x Height	169 x 86 x 43 mm
ESD Protection	8 kV Contact Discharge, 14 kV Air Discharge
Device grade	Industrial
NFC frequency	13.56 MHz
Standards	ISO/IEC 14443 Type A & B
Certification	NFC Forum
Wi-Fi frequency	2.4 GHz
Wireless standards	IEEE 802.11b, IEEE 802.11g, IEEE 802.11n
Wi-Fi security protocol	WPA2-PSK
Ethernet speed	10 Mbps, 100 Mbps
Connection Interface	I/O port, MSTB power connection, RS485 data interface port, RJ45 network port, USB-A
Comment	IP rating: IP3X



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry
