



## PANEL ANTENNA RRMT-W2-P-N-E



### ■ SPECIFICATION

PARAMETERS		VALUE
Frequency Range		2400 MHz ~ 2500 MHz
Bandwidth		83 MHz
Nominal Impedance		50 $\Omega$
VSWR, max		1.5
Half-power	Horizontal	30
Beamwidth	Vertical	30
Gain		14 dBi
Polarization		Vertical
Maximum Power		50 W
Operating Temperature Range		-40 °C ~ +60 °C
Lighting Protection		DC Ground
Antenna Dimensions		210 mm x 180 mm x 45 mm
Connector		N
Rated Wind Velocity		60 m/s
Weight		0.58 kg
Mounting		Wall hanging

### ■ APPROVAL

RS PRO	
DRAWN BY:	AR, June 1, 2018
APPROVED BY:	CP, June 1, 2018
REVISION:	A, Initial Release