





Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Board-to-Board Headers & Receptacles(97)



PCB Headers & Receptacles(97)



Rectangular Connector Housings(12)



Rectangular Power Connectors(106)



Standard Rectangular Connectors(12)

Customers Also Bought

TE Part #EC9833-000
ZHD-SCE-3.2-50-S1-4

TE Part #ASA158F12390235000
623 PLUG

TE Part #1-1415543-5
RTE44110

TE Part #1614770-4
BDS 2 A 250 10R 10%

TE Part #55992-1
TERMINAL,AMPOWER R 2/0 5/16

TE Part #ZPF000000000205373
PLUG MALE ANG.90 CAL.20 - FXP

TE Part #ZPF000000000136485
RECEPTACLE MALE FOR 12 PINS, CAL1,6

TE Part #ZPF000000000205388
CONTACT FEMALE CAL.20, M12 - FXP

TE Part #ZPF000000000205378
CONTACT MALE ANG.90, CAL20, 120MM2 - FXP

TE Part #YZ-KC-212751A-PY00
TOOL DISMOUNTING - FXP2

Documents



Product Drawings

V/R 2HDP+3LP+40S+4LP+2HDP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-6450869-6_D5.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-6450869-6_D5.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-6450869-6_D5.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English