

## Features

- Twin die sets for accurately crimping centre contact and rear ferrule.
- Compound-lever action multiplies hand force by 6 for less effort when crimping.
- Non-ratchet, cam action and precision-machined jaws.
- Jaws case hardened to HRC 58 for durability.
- Chemically blackened jaws and handles, with plastic grips for added comfort.

## RS PRO Crimping Tool For N Type Coaxial Cable Connectors

RS Stock No.: 405-304



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Crimps both centre contact and rear ferrule on N type coaxial cable connectors. Compound-lever action for one-handed operation. Plastic grips for added comfort.

Use when fixing N type connectors to RG-213/U coaxial cables. Ideal for engineers and technicians working in manufacturing, maintenance or repair of equipment used in:

- High-frequency signal transmissions.
- Telecommunications.
- Radio communications.
- Television broadcasting.
- Computer applications.

## General Specifications

Crimp Tool Type	Plier
Crimp Connector Type	N Type Connectors
For Use With	Use on N type connectors for RG-213/U coaxial cables.
Adjustable Ratchet	No
Finish	Chemically blackened jaws with soft plastic grips.
No. of Crimping Positions	2

## Mechanical Specifications

Overall Length	230 mm
Height Safe	No
Weight	625g