

DW721KN-QS

Radial Trails 2000W 300mm



5035048289099

Product Description:

Blade Ø / Bore (mm): 300 / 30 No-load speed (rpm): 3000 44445° cutting depth (mm): 60 90° cutting depth (mm): 90



Product features and benefits:

- Very rigid assembly of the column and the base supporting the arm
- High level of dust extraction thanks to 4 suction nozzles, wide design
- Arm in very resistant cast iron, carriage supporting the saw head guided by 4 ball bearings, ensuring precision and longevity of the machine
- The maintenance-free induction motor delivers high power even at maximum cutting capacities. Also available in a three-phase version with the reference DW722KN Pre-assembled and adjusted, delivered in a wooden box for maximum protection during transport, the machine is ready for use in a few minutes
- Simple graduations allow quick adjustment of the height of the cutting and cutting angles
- Radial saw with cutting capacity of 507 mm and a cutting depth of 90 mm

Specifications techniques :

- Power: 1580 W
- Power supply: 2000 W
- Blade diameter: 300 mm
- Maximum cutting capacity (90°/90°): 507 mm

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- 32-tooth carbide blade (x1)
- Blade Brake (x1)
- Base (x1)
- Assembly Tool (x1)
- Auto-return (x1)

