

FEATURES

- DIN rail
- Cold rolled steel construction
- Zinc coated and clear passivated
- Meets current BS, DIN and CENELEC standards
- Slotted and un-slotted variations

RS PRO, Slotted Din Rail, 500mm x 35mm x 7.5mm

RS Stock No.: 467-406



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, a selection of robust TS-35 standard DIN rails used for mounting various electrical and industrial equipment. The TS-35 rail or Top Hat as it is also known is manufactured from cold rolled steel which is then zinc coated and clear passivated. This ensures its strength and corrosion proof properties. Available in various lengths and slotted and un-slotted (perforated) profiles for easy attachment and wiring.

General Specifications

Compatibility	Top Hat
DIN Rail Type	TS35 Slotted
Applications	DIN rail terminal blocks, Power supplies, Plug in relays, Timer modules, Panel meters, I/O devices, Robotics, Automation and control devices

Mechanical Specifications

Material	Steel
Length	500 mm
Width	35mm
Height	7.5mm

Approvals

European Safety Standard	EN5022
---------------------------------	--------

