

Bulb Overview

	PART NO.	DESCRIPTION	TOTAL LENGTH(mm)	VOLTAGE	FOR USE WITH:										
	955 840 34	Bulb BA15d 5 W	42	12 V	200	203	209	641	800	840	845				
	955 840 35	Bulb BA15d 5 W	42	24 V	200	203	209	641	800	840	845				
	955 840 32	Bulb BA15d 5 W	42	30 V	200	203	209	641	800	840	845				
	955 840 57	Bulb BA15d 5 W	42	115 V	200	203	209	641	800	840	845				
	955 840 38	Bulb BA15d 5 W	42	230 V	200	203	209	641	800	840	845				
	955 015 34	Bulb BA15d 7 W	52	12 V	210	213	219	220	480	580	815				850
	955 015 35	Bulb BA15d 7 W	52	24 V	210	213	219	220	480	580	815	826			850
	955 015 36	Bulb BA15d 7 W	52	48 V	210	213	219	220	480	580	815	monit.			850
	955 015 37	Bulb BA15d 7 W	52	115 V	210	213	219	220	480	580	815				850
	955 015 38	Bulb BA15d 7 W	52	230 V	210	213	219	220	480	580	815				850
	955 826 35	Bulb BA15d 15 W	45	24 V	826										
	955 826 38	Bulb BA15d 15 W	45	230 V	826										
	955 827 35	Bulb BA15d 25 W	55	24 V	827										
	955 827 37	Bulb BA15d 25 W	55	115 V	827										
	955 827 38	Bulb BA15d 25 W	55	230 V	827										
	955 890 38	Bulb E14 15 W	76	230 V	890	895									
	955 880 66	Bulb E14 40 W	76	48 V	881										
	955 880 67	Bulb E14 40 W	76	115 V	881										
	955 880 68	Bulb E14 40 W	76	230 V	881										

Minimal differences in form are possible within the different bulb models.



	PART NO.	DESCRIPTION	TOTAL LENGTH(mm)	VOLTAGE	FOR USE WITH:
	955 890 55	Bulb E27 25 W	100	24 V	890 895
	955 890 67	Bulb E27 25 W	100	115 V	890 895
	955 890 68	Bulb E27 25 W	100	230 V	890 895
	955 883 34	Halogen bulb G 6.35 35 W	40	12 V	783 784 883 884
	955 883 35	Halogen bulb G 6.35 35 W	40	24 V	783 784 883 884
	955 885 24	Halogen bulb G 6.35 20 W	40	12 V	783 885
	955 885 25	Halogen bulb G 6.35 20 W	40	24 V	783 885
	955 880 34	Halogen bulb H 1 55 W	57	12 V	880
	955 880 35	Halogen bulb H 1 70 W	57	24 V	880
	956 x00 75	LED bulb BA15d	42	24 V	200, 203, 206, 209, 210,
	956 x00 67	LED bulb BA15d	42	115 V	213, 216, 219, 220, 223,
	956 x00 68 x see page 182	LED bulb BA15d	42	230 V	641, 805, 840, 846, 850, 851, 852
	956 x20 75	LED bulb E27	65	24 V	890 895
	956 x20 67	LED bulb E27	65	115 V	890 895
	956 x20 68 x see page 183	LED bulb E27	65	230 V	890 895

Minimal differences in form are possible within the different bulb models.

