

## **B1005 - K-Jump/ K-Trek/ K-Rush S1P HRO SRC**

**Collection:** Kaptiv

**Upper:** Breathable Fabric

**Lining:** SmellStop Antiodor and Antibacterial\*

**Midsole:** Fresh'n Flex

**Toecap:** Aluminium

**Sole:** Double-Density PU/HRO Rubber i-daptive® Technology

**Outer Carton:** 10

### **Kaptiv**

The first safety footwear range with stability control, designed to offer incredible dynamic comfort.



### **Standards**

UNI EN ISO 20345:2012 S1P (HRO SRC)

### **Features**

- Anti-static footwear
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Heat resistant 1 minute up to 300°C
- Hydrocarbons resistant
- Men's width
- Women's width
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191

# PORTWEST®



## B1005 - K-Jump/ K-Trek/ K-Rush S1P HRO SRC

**Commodity Code: 6404199000**

### Test House

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)  
Via Alberto Riva Villasanta, 3  
, Italy  
Cert No: F-113-00280-18 rev.01

### Carton Dimensions/Weight

| Item       | Colour       | Len  | Wid  | Hgt  | Weight(Kg) | Cubic(m <sup>3</sup> ) | EAN13         | GTIN/DUN14 |
|------------|--------------|------|------|------|------------|------------------------|---------------|------------|
| B1005BKY36 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.1800     | 0.0989                 | 8054633494394 |            |
| B1005BKY37 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.2000     | 0.0989                 | 8054633494400 |            |
| B1005BKY38 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.2500     | 0.0989                 | 8054633494417 |            |
| B1005BKY39 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.3100     | 0.0989                 | 8054633493687 |            |
| B1005BKY40 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.3100     | 0.0989                 | 8054633493694 |            |
| B1005BKY41 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.3500     | 0.0989                 | 8054633493700 |            |
| B1005BKY42 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.4400     | 0.0989                 | 8054633493717 |            |
| B1005BKY43 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.4800     | 0.0989                 | 8054633493724 |            |
| B1005BKY44 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.5400     | 0.0989                 | 8054633493731 |            |
| B1005BKY45 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.5900     | 0.0989                 | 8054633493748 |            |
| B1005BKY46 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.6100     | 0.0989                 | 8054633493755 |            |
| B1005BKY47 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.6440     | 0.0989                 | 8054633493762 |            |
| B1005BKY48 | Black/Yellow | 67.0 | 41.0 | 36.0 | 1.7000     | 0.0989                 | 8054633493779 |            |