



**Part Number :** [1300190001](#)

**Product Description :** Die Block 2 Pole Angle Receptacle, Yellow

**Series Number :** 130019

**Status :** Active

**Product Category :** Circular Industrial Connectors

**Engineering Number :** 22801



---

## Documents & Resources

### Drawings

[1300190001\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)4578-DC (25 June 2020)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[UKCA - Declaration of Conformity](#)

[CE - Declaration of Conformity](#)

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	130019
Description	Die Block 2 Pole Angle Receptacle, Yellow
IP Rating	N/A
Product Name	Die Block
Type	Die Block
UPC	78678822801

### Agency

CSA	LR6837
UL	E46237

### Electrical

Current - Maximum per Contact	25.0A
Voltage - Maximum	600V AC

### Physical

Coupling Type	Push to Lock
Gender	Female
Keyway	None
Length	N/A
Material - Component	Nitrile/PVC
Mounting Thread Size	N/A
Net Weight	194.137/g
Orientation	N/A

Panel Mount	N/A
Poles	2
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A