

PRODUCT-DETAILS

# C10-6-SK

## TERMINAL RING TONGUE



### General Information

Extended Product Type	C10-6-SK
Product ID	7TAI029580R0019
EAN	5414363148944
Catalog Description	TERMINAL RING TONGUE
Long Description	Non-Insulated Ring Terminal, Length .82 Inches, Width .31 Inches, Bolt Hole #6, Wire Range #12-#10 AWG, Copper, Tin Plated

### Ordering

EAN	5414363148944
UPC	786210803401

### Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	1.63 in 41 mm
Package Level 1 Height	3.5 in 89 mm
Package Level 1 Depth / Length	2.63 in 67 mm
Package Level 2 Units	250 piece
Package Level 2 Width	9.4 in 239 mm

Package Level 2 Height	8.9 in 226 mm
Package Level 2 Depth / Length	15.1 in 384 mm
Package Level 3 Units	2500 piece
Package Level 3 Width	6 in 152 mm
Package Level 3 Height	7.1 in 180 mm
Package Level 3 Depth / Length	8.39 in 213 mm

## Additional Information

Brand / Label	Sta-Kon
Color	Metallic
Effective Date	19960423
Material	Copper
Number of Batteries	0
Product Name	STA-KON AND CATAMOUNT TERMINAL
Product Type	Non-Insulated Ring Terminal
Special Functions	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Standards	UL E9809
Voltage Rating	600 V
Wire Size	12-10 AWG

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	C10-6-SK
Instructions and Manuals	C10-6-SK

## Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
ETIM 7	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

