

7412-01

Rectangular reversible ratchet head

9x12

Code	ETIM
7686500	EC002218
EAN	UNSPSC
4002805742013	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82079099	



Article description

- For solving difficult assembly problems, easily replaceable
- Forged
- Chromium vanadium steel
- Matt chrome-plated
- With locking pin
- Fine-toothed
- Return angle 5°
- Max. continuous load of ratchet according to DIN EN ISO 6789:2003 and/or maximum load of cavity

Article information

Contents (Qty of pieces)	1	Number of teeth	72
Net weight [kg]	0,14 kg	Continuous load	3/8" = 135 N·m
Total width [mm]	34 mm	Depth gauge [metric]	17,5 mm
Material	Chrome-vanadium steel	Width of head \geq [mm]	34 mm
Drive connector square (male)	3/8"	Head height \geq [mm]	23,2 mm
Drive connector square (male)	10 mm	Drive connector rectangular	9 x 12 mm
Return angle	5°		