

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936013987](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 24B «104x27», M32 Thread, High Construction, Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size 24B «104X27»
 Component Type Double Lever SMT Housing
 IP Rating IP66
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
 Type STD
 UPC 887191874517

Physical

Housing Coating Polyester Powder
 Housing Color Grey RAL 7037
 Lock to Mating Part Yes
 Material - Gasket NBR
 Material - Housing Die-cast Aluminum
 Material - Lever Galvanized Steel
 Mounting Style Surface Mount
 Net Weight 489.000/g
 Number of Levers 2
 Packaging Type Bag
 Thread Size M32
 Thread Type (M) Metric

Electrical

Voltage (Up to): EN 61984: 500V, UL/CSA: 600V

Material Info

Engineering Number 7824.7478.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000400780_00_000.pdf

Search Parts in this Series

[93601 Series](#)

Use With

Inserts with voltage up to 600V and with modular inserts