

Fast Dry Hand Dryers



Jet Dry® Plus

Automatic double sided high speed jet hand dryer.

- 99.9% HEPA Filter
- UV Sterilisation
- 10 second dry time
- LED indicator
- Removable drip tray
- Lo-Carbon DC Motor, 750W - 2050W
- Ambient Temperature Response Element
- Air speed 95m/s
- Antibacterial coating
- Heater Element 900 - 1300W, adjustable/On/Off
- 700 x 300 x 225mm (H x W x D)
- Weight 9.5kg
- IPX4 Rated
- Sound level: 75dB(A) at 1m
- GS approved
- Cable entry bottom right

Models

Silver

White

Stock Ref

409117

409118



Lo-Carbon eTempest

Automatic hand dryer for fast drying applications.

- 10 second drying time
- Automatically senses work surfaces to avoid nuisance running
- Insulation Earthed Class 1
- Cover: Steel 1.2 mm thick, epoxy coated
- 180 x 250 x 138.5mm (H x W x D)
- Weight: 3.8Kg
- Heater element 500 Watts, adjustable/On/Off
- Unique blue dry zone indicator
- Infrared automatic operation
- Rated at 500kW - 1.2 kW at 230V
- Airflow 113m³/h
- 60 seconds auto shut off
- IPX1 Rated
- Motor: Max 30,000rpm brushed motor
- Soft start
- GS Approved
- Cable entry bottom left

Stock Ref

444956



Tempest®

Automatic no-touch hand dryer for heavy duty applications.

- 10 second drying time
- Automatically senses work surfaces to avoid nuisance running
- Unique blue dry zone indicator
- Cover: Steel. Finish: Polished or satin stainless steel
- Insulation Earthed Class 1
- 277 x 201 x 175mm (H x W x D)
- Weight 6.6kg (packaged)
- Airflow 116m³/h
- Rated at 500W - 1.6kW at 230V
- Heater Element 450 - 900W, adjustable/On/Off
- Infrared automatic operation
- 60 second auto shut off
- IP23 Rated
- Motor speed adjustable
- Motor: Max 18,000rpm brushed motor
- Soft start
- Sound Level: 78dB(A) at 1m
- GS Approved
- Cable entry bottom left

Models

Satin Stainless

Polished Stainless

White

Filter Assembly Pack

Filter Replacement 2 pack

Stock Ref

439464

439463

437231

444959

444960

