

## FEATURES

- 4 to 6 tread options
- Average working heights from 2440mm to 2900mm
- Retractable castors
- Manufactured from steel tube offering excellent durability
- Steps/treads formed from steel sheet
- Supplied with ribbed rubber anti-slip treads/steps
- Epoxy powder coated finish in red
- Weight: 28Kg to 36kg

## RS PRO 4 Tread Steel Steps 0.915m Platform Height, Red

RS Stock No.: 909-7078



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Introducing heavy duty commercial steps from RS PRO, a range of high quality and robust steps ideal for use in a variety of environments. This range of safety steps are manufactured from tubular steel and feature an epoxy powder coat, offering excellent durability and corrosion resistance. The steps include spring loaded castors that retract once pressure is applied, allowing them to remain mobile whilst maintaining stability when in use. The treads feature ribbed rubber anti-slip grips providing a high quality grip, preventing the user from slipping. The treads are accompanied with double hand rails to assist with ascending and descending the steps, whilst the anti-slip rubber feet help to keep the steps stable and securely in place. These heavy duty mobile steps are available with either 4, 5 or 6 treads to suit your needs.

What sizes are available?

- 4 Tread: [9097078](#)
- 5 Tread: [9097072](#)
- 6 Tread: [9097081](#)

## General Specifications

Number of Steps	4
Material	Ribbed Rubber, Steel
Colour	Red
Applications	Warehouse, Factory, Retail, Distribution, Automotive cleaning and maintenance

## Mechanical Specifications

Overall Dimensions	1760mm x 640mm x 850mm
Overall Height	1760mm
Overall Width	640mm
Overall Depth	850mm
Weight	28kg

Platform Dimensions	
Height	915mm
Width	560mm
Depth	340mm



Full Choice/Range Available			
No. of Treads	O/A HxWxD Size (mm)	Platform Size HxWxD Size (mm)	RS Stock No
4	1760 x 640 x 850	915 x 560 x 340	9097078
5	1985 x 640 x 1000	1145 x 560 x 340	9097072
6	2230 x 640 x 1170	1400 x 560 x 340	9097081