

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936030044](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect Connector Kit, 6 Pole, Series S-E Female-Male Inserts, M20 Metal Cable Gland, M20 Die-cast Aluminum Hood-Top Entry, Bulkhead Housing, 1 Lever, Vertical, Size 6B «44x27», Grey

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Kit components**

Kit Components [936000046](#) M20 Gland, [936010917](#) M20 Hood, [936010215](#) Male Insert, [936010207](#) Female Insert, [936010842](#) Vertical Bulkhead Housing

**General**

Product Family Industrial Connectors / Enclosures  
 Series [93603](#)  
 Color - Cable Jacket N/A  
 Component Size 6B «44x27»  
 Component Type Connector Kit - Female+Male  
 Insert Series S-E  
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
 Product Category Heavy Duty Connectors  
 Product Name GWconnect  
 UPC 887191862231

**Physical**

Lock to Mating Part Yes  
 Mounting Style Bulkhead  
 Net Weight 330.000/g  
 Packaging Type Bag  
 Thread Size M20  
 Thread Type (M) Metric

**Electrical**

Current - Maximum per Contact 16.0A  
 Voltage - Maximum 500V

**Material Info**

Engineering Number 7906.7754.5



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
 D(2022)4187-DC (10  
 June 2022)

Lead

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

**China RoHS**

Green Image

Not Relevant

Not Contained

CER\_4000400780\_00\_000.pdf

**Search Parts in this Series**

[93603](#) Series