

0-20-201

INSTANTCHANGE SAW BLADE - 1 JET CUT BLADE ARMOR FLOW
CUTTER 500MM BLADE - FATMAX PRO



3253560202019

Product Description:

Blade-Armor blade treatment: Anti-corrosion protection and reduced friction during cutting - INSTANTCHANGE system - 7 teeth/inch teeth



Product features and benefits:

- 7 TEETH/INCH: for high-performance sawing applications INSTANT
- CHANGE™ : for use with the STANLEY® FATMAX® InstantChange™ system which allows for easy changes of blade in seconds.
- BLADE ARMOR® COATING: reduces friction for faster cutting and provides good corrosion resistance TRIPLE SHARPENING TEETH: for faster cutting and more effective
- REUSABLE BLADE GUARD : protects the blade during the transport
- BLADE THICKNESS, 1MM: Reduces blade flex, ensuring maximum power transfer with each stroke and improving cutting accuracy
- INDUCTION HARDENED TEETH: stay sharp longer
-

Product Warranty:

This product is covered by the legal warranty

Specifications techniques :

- Blade Thickness: 1 mm Blade Length
- [Imperial]: 20 in
- Tape length: 500 mm

