



Application Range

EMC Earthing gland, for applications where electrical interference fields can occur. Medical engineering, frequency convertors, measurement and control technologies.

Technical Data

Material: Body: Nickel Plated Brass
Earthing Sleeve: Plain Brass
Seal: CR/NBR
O Ring: NBR

Protection Rating: IP68

Temperature Range: -30°C to +80°C

Article List

Part Number	Description	Thread Size	Clamping Range Inner Sheath (mm)	Clamping Range Outer Sheath (mm)	Spanner Wrench (mm)	Thread Length (mm)
59000320	Cable gland, metal, EMC	20mm	5.5 – 7	8.5 – 10.8	22	13
59000340	Cable gland, metal, EMC	20mm	7 – 9	10.8 – 12.8	24	13
59000350	Cable gland, metal, EMC	20mm	8 – 10	10.8 – 12.8	24	13
59000370	Cable gland, metal, EMC	25mm	10 – 12	14 – 15.8	30	13
59000430	Cable gland, metal, EMC	32mm	16 – 18	19.5 – 21.8	40	13