

module Ethernet/IP slave - 2 x RJ45 connectors

VW3E704100000

EAN Code: 3606485306957

Main

Range of product	Modicon LMC078	
Product or component type	Ethernet/IP network module	
Range compatibility	Modicon LMC078	
Product compatibility	Motion controller	

Complementary

Physical interface	RJ45
Port Ethernet	10BASE-T/100BASE-T
Communication service	Ethernet/IP adapter
Integrated connection type	Ethernet/IP - 2 RJ45 connector, transmission rate: 100 Mbit/s

Environment

Standards	EN/IEC 61131-2 zone B CSA C22.2 No 142 UL 508
Product certifications	CSA CE cULus
Marking	CE
Ambient air temperature for operation	555 °C
Ambient air temperature for storage	-2570 °C
Relative humidity	595 % without condensation
IP degree of protection	IP20 conforming to IEC 61131-2
Pollution degree	2
Operating altitude	02000 m
Vibration resistance	10 m/s² on direct mounting
Shock resistance	100 m/s²

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.700 cm
Package 1 Width	8.300 cm
Package 1 Length	11.100 cm

Package 1 Weight	93.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	50
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.124 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Take-back

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
Use Again	
○ Repack and remanufacture	

No