

Combination Lock 2800



Product Description

The 2800 mechanical combination lock is a 4 wheel combination lock featuring up to 10,000 unique combinations. With a robust design this combination lock is available with a range of options including single-use public mode, private mode* and wet area versions.

- **Versions:**
 - Public and private mode available
 - Standard fit with countersunk screws
 - Twist resist with pan head screws
- **Movement:**
 - 1 - Right Hand (clockwise to open)
 - 2 - Left Hand (anti-clockwise to open)
- **Construction:** Zinc die-cast construction
- **Combinations:** 4-Wheel combination (10,000 codes)
- **Code finding feature:** 10 Disc barrel with shutter cap
- **Code changing function:** only accessible in the un-locked position
- **Finish:**
 - Powder coated finish
 - Body - black as standard
 - Face - white, silver or black as standard
- **Diameter:** 56 x 28mm (protrudes from door frame)
- **Nut fixing:** 3/4" - 27 UN x 20mm long (15.9mm A/F)
- **Cam fixing:** 8mm Sq. with M4 thread
- Epoxy logo badge (customer logo available on request)

Options

Product Code	Housing Fixing	Body Width	Body Depth	Cam Fixing	Lock Feature	Code Combinations	Body Length
2800	Nut Fixing	56	28	Screw	Standard	10000	20

Technical Drawing

