



Product data sheet

Power tools for trade & industry

Cordless Jobsite Light

PRO GLI18V-1500



Superior 1500-lumen brightness with rugged design for consistent performance

The most important data

Battery voltage, works with	18.0 V
Luminous flux	1,500 lm
Weight excl. battery	1.4 kg

Part Number 0 601 4A8 000

Technical data

Technical data

Weight excl. battery	1.4 kg
Luminous flux	1,500 lm
Number of brightness levels	2
Packaging dimensions (width x length x height)	223 x 247 x 137 mm
Battery voltage, works with	18.0 V

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High performance with 1500 lm brightness
- Robust and rugged with IP 64-rated protection against dust and water splashes
- Quick and easy mounting on tripod, workbench or any other surface for hands-free lighting
- Versatile brightness with two modes to choose from: 1500 lm and 800 lm



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

