

FEATURES

- 6.3mm x 32mm cartridge size
- F Speed Rating
- Cylindrical in shape
- HBC (high breaking current) fuse

RS PRO, 20A Ceramic Cartridge Fuse, 6.3 x 32mm, Speed FF

RS Stock No.: 247-3955



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Cartridge Fuses



Product Description

RS PRO offer this range of miniature ceramic cartridge fuses which are either ultra-rapid fuses (FF) or fast acting fuses (F). The ultra-rapid fuses operate at higher temperatures so are ideal to provide circuit protection to semiconductor devices. The fast-acting fuses are ideal to protect less sensitive components.

General Specifications

Fuse Speed	FF
Body Material	Ceramic
Size Designation	Miniature
Applications	Industrial, Commercial, Home/Residential, Automotive

Electrical Specifications

Current Rating	20A
Voltage Rating	500V ac
High Rupture Capacity	Yes
Breaking Capacity (at Maximum Voltage Rating)	50kA @ AC 500V
Voltage Drop	300mV
Power Dissipation	11W
l²t Value	46 A ² s

Mechanical Specifications

Fuse Size	6.3mm x 32mm
Overall Length	32mm
Diameter	6.3mm




Approvals

Compliance/Certifications

UL, RoHS







Time-Current Characteristics

