

FEATURES

- LED floodlight
- Voltage of 240 V ac
- Wattage of 20 W
- IP65 for protection against water and dirt ingress
- One LED
- Luminosity of 1800lm
- Colour temperature of 4000 K
- Dimensions of (H) 118 mm x (W) 163 mm x (D) 29 mm
- Lifespan of around 30,000 hours
- Lamp supplied
- Beam angle of 105°
- Aluminium case

RS PRO Floodlight, 20 W, 1800 lm, IP65 240 V

RS Stock No.: 145-5880



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO LED (light-emitting diode) floodlight lets you illuminate your outdoor space. This product is often used as a security light in both residential and commercial settings. It has dimensions of (H) 118 mm x (W) 163 mm x (D) 29 mm. The LED has a 4000 K (kelvin) colour temperature and emits a cool white glow. It has a high luminosity of 1800 lm (lumens). This bulb has been built to last 30,000 hours, making it more economical than its lifespan-limited halogen counterparts. It's contained within an IP65-rated unit for protection against water and dirt ingress.

General Specifications

Floodlight Type	Outdoor
Luminosity	1800 lm
Colour Temperature	4000K
PIR Included	No
Beam Angle	105°
Case Material	Aluminium
Housing Colour	White
Applications	Warehouses, Car Parks, Walkways, Construction areas, Parks and gardens, Home security

Electrical Specifications

Wattage	20W
Voltage	240V
Lamp Type	LED
Life Hours	30000h
Lamp Supplied	Yes

Mechanical Specifications

Dimensions	118mm x 163mm x 29mm;
Height	118mm
Width	163mm
Depth	29mm

Operation Environment Specifications

Operating Temperature Range	-20°C to 40°C
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	40°C

Protection Category

IP Rating	IP65
-----------	------

Approvals

Compliance/Certifications	EN61340
---------------------------	---------



