

Part Number: **5530123F**

## General Description

Series	553
Configuration	3 mm Lens
Description	3 mm Green/Yellow Bi-Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	45
LED Centerline	2.54mm





This is a  
RoHS Compliant Product  
[To learn more click here](#)

## Absolute Maximum Ratings (Ta = 25°)

Solder Temperature	260 for 5 secs
Operating Temperature	-25 to +85
Storage Temperature	-30 to +100

## Operating Characteristics

	LED Position: 1	LED Position: 2
Color	 Green	 Yellow
LED Type	High Efficiency	High Efficiency
Peak Wave Length	563	585
Luminous Intensity Min	5.6	2.2
Luminous Intensity Typical	16	6.3
Forward Voltage Typical	2.1	2.1
Forward Voltage Max	3	3
Power Dissipation Max	75mW	60mW