

EXAWATT50 – ref 798756

Portable Power Station High power 4500W

Product Overview

- Transportable power station designed for intensive use
- Its high-power output and robustness make it the perfect alternative to the generator set



Product Benefits

- **4500W power output:** Allows you to power all types of tools indoors and outdoors
- **LFP 5120Wh battery:** Long battery life and lifespan (3000 minimum charge/discharge cycles)
- **Very robust and very easy to use:** Designed for intensive daily use. Its metal shell and numerous protections allow you to work in complete safety.

Technical Specifications

GENERAL FEATURES

- Battery Energy: 5120Wh (51.2V-100Ah)
- Battery Type: LFP Lithium Iron Phosphate (80% of initial charge available after 3000 full charge & discharge cycles)
- 230 V inverter: 4500W pure sine
- Peak power 5500W
- EPS (Emergency Power System) Mode
- Display: LCD display showing % of battery remaining, charging and discharging power
- Operating Temperature:
Discharge (-20/+60°C) - Charge (0/+50°C)
- Dimensions (LxWxH): 622 x 420 x 520 mm
- Weight: 65.6 kg

CHARGING MEANS

- Mains: Cable provided (3h00)
- Solar panel: Not included: up to 1600W max (Voc panel: 12-68V)

OUTPUTS

- AC 230V sockets x 2:
* 3600W max per socket (Crete 60 sec: 5500W)
* 4500W in total (Crete 60 sec: 5500W)
- DC 12V Cigarette Lighter Socket x 1: 120W max
- USB-A fast charging x1: 5V 18W max USB-C x 1 to 100W max

Compliant pannels : 315W (#39211), 400W (#39212), 200W (39255), 440W (798770)

Logistics

EAN	3545417987560
Packing height	71 cm
Packing Length	69,5 cm
Packing Width	48 cm
Weight packing	80 kg
Type Packaging	Wooden box
PCB	1
Customs Code	

