



ENGLISH

Datasheet

RS Pro Fixed Plate Castor, 20kg

RS Stock No: **446-2058**



Product Details

RS Pro fixed castor has load capacity of 20 kg. This low level castor is suitable for fitting to office equipment, test gear etc.

Features and Benefits

- Bright zinc plated pressed steel fixed castor
- For fitting to office equipment, test gear and more
- Unbraked

**Specifications:**

Application	Industrial
Fixing Centres (Length)	35 mm
Fixing Centres (Width)	35 mm
Fixing Centres	35 x 35 mm
Fixing Hole Size	5 mm
Fixing Plate Dimensions	58 x 57 mm
Fixing Plate Length	58 mm
Fixing Plate Width	57 mm
Hub Bearing Type	Plain Bore
Hub Material	Steel
Includes Brake	No
Load Capacity	20 kg
Number of Fixing Holes	4
Overall Height	71 mm
Rotation	Fixed
Tyre Material	Rubber
Wheel Diameter	50 mm
Wheel Width	19 mm