

IN 19 LK 6-140

Screwdriver bit socket 1/2"

with ball end, for in-hex screws, long pattern

Code	ETIM
6162810	EC002157
EAN	UNSPSC
4010886616284	27-11-17-01
Country of origin	eCl@ss
Germany	21-04-04-02
Customs tariff number	
82079030	



Article description

- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- Total swivel angle approx. 15-20°

Article information

Contents (Qty of pieces)	1	Standard	DIN 3120 - C 12,5 ISO 1174
Net weight [kg]	0,091 kg	Width across flats l [mm]	6
Total length [mm]	140 mm	Backup	Ball Catching Cricket
Surface	chrome-plated	Tip length	102,0 mm
Material	Chrome-vanadium steel	Insert Ø Actuator	22,5 mm
Drive connector square female [metric]	12,5 mm	Total swivel angle	15 - 20°
Drive connector square female [inch]	1/2"		