



**Fuse holder, low voltage, 30 A, AC 600 V, 10 x 38 mm, CC, 2P, UL, with indicator**

**Part no. 2P 10X38MFH 30A 600V Class CC-indicator**  
**Catalog No. CHCC2DIU**

## Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	30
Rated voltage			AC 600 V
Size			10 x 38 mm
Utilization category			CC
Status indicator			with indicator
Description			DIN rail mounting colour-coded Rated for use with 75°C or 90°C wire fine stranded wire spade terminals and with comb-bus bars Use any higher temperature rated wire with appropriate derating. Modular
Number of poles			2P
usable for size/applications			for cylindrical fuse-links
Standard/Approval			UL
Standards/Regulations			IEC cULus CCC CSA UR

## Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss10.0.1-27-14-21-21 [ADI305007])			
Nominal voltage		V	600
Mounting method			DIN rail
For fuse size			10x38 mm
Number of poles			2
Concurrently switching N-neutral			No
Lockable			Yes
Optical defect indication			Yes
Width in number of modular spacings			2
Built-in depth		mm	45.1
Degree of protection (IP)			Other