

Mureva FIX - instacable for Ø40-63 mm conduits - with Murafix plug

ENN47963

! Discontinued on: 25 Sept 2024

! Discontinued

Main

range of product	Mureva
Product or component type	Conduit support
colour	Grey (RAL 7035)
quantity per package	100 pieces

Complementary

Accessory / separate part category	Installation accessory	
Condition of use	Indoor	
Tube diameter	4063 mm	
Thread type	M8	
Material	PA (polyamide) 6/6	
Fixing mode	By Murafix plug By screw	
Net weight	0.008 kg	

Environment

operating temperature -40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.000 cm
Package 1 Width	0.150 cm
Package 1 Length	35.000 cm
Package 1 Weight	10.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	800
Package 2 Height	40.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	8.000 kg

Unit Type of Package 3	P12
Number of Units in Package 3	9600
Package 3 Height	132.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	107.000 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No