



Frame paneling IP30, W: 800 mm

Model	
product brand name	SIVACON S4
product designation	rack cladding
Protection class	
protection class IP	IP30
suitability for use for outside use	No
Appearance	
color	light grey
Mechanical Design	
height	1 975 mm
width	800 mm
depth	25 mm
installation location	in the field
net weight	5 500 g
material	sheet-steel
Approvals Certificates	
General Product Approval	other



[Miscellaneous](#)



[Miscellaneous](#)

other	Environment
Confirmation	Environmental Con- firmations
	Environmental Con- firmations

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2197-8BA11 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/8PQ2197-8BA11 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2197-8BA11 CAX-Online-Generator

last modified:

4/30/2025 

