

DRF 0812N

- Part number : DRF 0812N
- Box type : Closed
- Box material : Metal
- Swivel included : 180°
- Hose material : Polyurethane / PVC
- ID hose : 8 mm
- OD hose : 12 mm
- Hose length : 12 m
- Threads : 1/4 BSP male
- Thread non scratch protection
- Maxi temperature : +70°C
- Working pressure : 12 b
- Inlet hose included
- Weight : 5.8 kg

