

6673342



7" neutral American type, curved jaws with wire cutters (CRV, nickel plated)

total length:185MM+-13,head width:56MM+-6,handle width:47.8MM+-6.5,head thickness:8.5MM+-2.5,head length:26MM,jaw capacity>=35