


Technical data sheet

Article number:
132-37510

CT375



Product Group	Cable ties for single hole application
Product Family	CT-Series with square head, 700 N loop tensile strength
Material	Polyamide 6.6, heat stabilised (PA66HS)
Colour	Black (BK)
Application Range	High Temperature and Outdoor Use
Bundle Ø max.	100 mm
Fixation Method	Others
Flammability	UL 94 V2
Height (H)	1.5 mm
Length (L)	375 mm
Min.Tensile Strength	700 N
Operating Temperature	-40 °C to +105 °C
Package Content packed in	bag
Pack Cont.	50 pcs.
Releasable Closure (Yes/No)	No
Thickness (T)	1.5 mm
Variant	Outside Serrated
Weight/Unit	0.004958 kg
Width (W)	7.6 mm

RoHS