

Features

- Long lasting power
- Stable operating voltage
- 12V high voltage alkaline
- Excellent reliability and high capacity
- In accordance with IEC60086-1 and IEC60086-2

RS PRO Specialty Size Batteries

RS Stock No.: 0194087



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This high voltage alkaline batteries key applications consist of keyless entry remotes, toys, car key fobs, security device smoke alarms and electronic organizers.

In tune with the most advanced remote-control apparatus, these batteries are especially built to conform to the highest standards of performance excellence in remote controls for cars, photo equipment and other electronic devices. To give maximum endorsement they hold a stable operating voltage throughout use.

General Specifications

Chemistry	Alkaline-Manganese Dioxide Battery
Number Of Cells	1
Terminal Type	Standard
Model No.	LR23A, MN21, IEC 8LR932, ANSI:1811A
Shelf Life	2 years
Application	Remote Controls, Toys, Car Key Fobs.
Size	A23
Number Of Batteries Supplied	1

Electrical Specifications

Nominal Voltage	12V
Capacity	55mA (Test condition:20KΩ Load, continuous discharge, and end voltage 6.0V)
Open circuit voltage	12.0Volte +0.4/-0
Average weight	8±0.2g

Mechanical Specifications

Height	28.10±0.15mm
Diameter	10.10±0.10mm
Relative Humidity	75%

Operation Environment Specifications

Storage Temperature Range	0°C to 45°C
---------------------------	-------------

Approvals

Compliance/Certifications	Regulation (EU)2023/1542
---------------------------	--------------------------

