

# TECHNICAL SPECIFICATION



## Stealth™ 16G

Clear K & N Rated / ASA920-1A1-300



### DESCRIPTION

Stealth™ 16g is our lightest safety eyewear, weighing only 16g. The spectacle features next generation ultra-thin and ultra-strong optically perfect lenses moulded using the latest technology to deliver a thinner lens while maintaining performance. The Stealth™ 16g spectacle's flexible frame with vented side arms enhance comfort and fit.

### OPTIONS

Amber K Rated (ASA920-161-200)

**Clear K & N Rated (ASA920-1A1-300)**

Clear K Rated (ASA920-161-300)

Smoke K Rated (ASA920-163-000)

### SAFETY STANDARDS

EN 170 • EN 166



JSP Limited, Worsham Mill, Minster Lovell, Oxford OX29 0TA, England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: [sales@jspsafety.com](mailto:sales@jspsafety.com) / Web: [www.jspsafety.com](http://www.jspsafety.com)

Do Not Publish without written permission from JSP Limited. Contact [copyright@jspsafety.com](mailto:copyright@jspsafety.com). Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 1 of 2 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.



## SPECIFICATIONS



Product Weight  
16g



LIGHT TRANSMISSION BREAKDOWN Lens Shade number  
1.2



Optical Class (1 – Class 1 – High quality for regular use. 2 – Class 2 – Medium quality for occasional use. 3 – Class 3 – Low quality for exceptional use)  
1



The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures. (-5°C and +55°C) Optional  
T



Resistance to fogging (optional)  
N



RADIATION PROTECTION BREAKDOWN filtering effect  
Scale Number  
2C



Manufacturer's Trademark  
JSP Dagger



Low Energy Impact resists a 6 mm, 0.86g ball @ 45 m/s °  
Maximum protection for glasses  
F



Resistance to Surface Damage by Fine Particles (optional)  
K

## FEATURES



### Quality Lens

Dual 9.5 base, ultra-thin & ultra-strong optically perfect lenses. Because they are so thin they transmit more light than other spectacles, improving vision and lowering eye strain.



### Integral Nose Bridge

The built-in nose bridge has been designed and shaped to fit most face shapes comfortably and securely.



### Spectacle Cord Anchor

The temple tips have a spectacle cord anchor point for further practicality, preventing loss or scratching from being put on rough surfaces.

## RANGE

**STEALTH**  
**16g**

## VIDEOS



[youtu.be/ak34PrVrAH8](https://youtu.be/ak34PrVrAH8)

## DOWNLOADS



[Image Pack \(ZIP\)](#)



[doc-stealth-16g.pdf \(PDF\)](#)



JSP Limited. Worsham Mill. Minster Lovell. Oxford OX29 0TA. England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: [sales@jspsafety.com](mailto:sales@jspsafety.com) / Web: [www.jspsafety.com](http://www.jspsafety.com)

Do Not Publish without written permission from JSP Limited. Contact [copyright@jspsafety.com](mailto:copyright@jspsafety.com). Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 2 of 2 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.

