

Specifications

Photo is representative

Eaton 32ET

Eaton Bussmann series high speed British standard fuse, Single barrel, 32A, 690 VAC/500 VDC (IEC), 700 VAC/500 VDC (UL), Class aR, Breaking capacity 200 kA RMS Sym.HS, 50 kA DC at 500 VDC

General specifications

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	32ET
EAN	5027590476676
UPC	051712833912
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	41.4 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated Designed and tested to BS88 part 4 IEC 60269-4

Electrical data

AMPERAGE RATING	32 A
VOLTAGE RATING	690 V (IEC), 700 V (UL)
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	500 V
INTERRUPT RATING	200 kA RMS Sym, 50 kA at 500 Vdc
CLASS	Class aR
PRE ARC (I2T)	32
CLEARING (I2T)	190
WATT LOSSES	11 W

Compatible Trip indicator/Microswitch

SUITABLE FOR	EC-600 Trip indicator kit (indicator + clips) TI700 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
---------------------	---

Product specifications

APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE INDICATOR	None

Resources

BROCHURES	eaton-bussmann-series-bs88-high-speed-fuses-product-aid-pa135003en-us.pdf
CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf
DECLARATIONS OF CONFORMITY	eaton-high-speed-british-standard-fuse-declaration-of-conformity-eu250044en.pdf eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250922en.pdf
MCAD MODEL	eaton-hs-bs88-body-fuses-mcad-3d-models-8-80a-et.stp
TECHNICAL DATA SHEETS	720024 CT, ET, FE, EET, FEE, FM, FMM, MT, MMT fuses

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

