

# Eaton 12ADFHA25

Catalog Number: 12ADFHA25

Air fuse-link, medium voltage, 25 A, AC 12 kV, 51 x 254 mm, back-up, BS, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	12ADFHA25  EAN 5027590430319
Product Length/Depth	Product Height
254 mm	50.8 mm
Product Width	Product Weight
50.8 mm	1500 g
Certifications	
BS 2692-1	

## Product specifications

## Resources

### Used with

A3354710 Fuse clip

### Type

Fuse

### Application

protection of primary side  
transformers  
used in fuse switch  
combination units, fuse  
bases and fuse switches

### Amperage Rating

25 A

### Fuse indicator

With Striker

### Fuse size

51 x 254 mm

### Breaking capacity

12 kA

### Installation technique

Air

### Performance Cat According To IEC 60282-1

Back-up

### Product application

Primary side transformer protection

### Rated frequency - max

50 Hz

### Rated frequency - min

50 Hz

### Release characteristic

Other

### Standard

British Standard

### Utilization category

Other

### Voltage type

AC

With striker

Yes

Class

Class back-up

Fuse shape

Cylindrical

Pre arc (I<sup>2</sup>T)

5.1 x 102

Resistance

28.3 ohms

Fuse diameter

51 mm

Interrupt rating

12 kAIC

Construction size

51 x 254 mm

Mounting method

Clip-in

Voltage rating

12 kV

Fuse type

ADFH



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia